

IV Rail




- IV rail designed for easy use and safety.
- Ceiling-suspended for easy attachment and removal of IV bottle hangers.
- Various combinations possible for a wide range of applications.


IV Rail

Conventional IV Rail


Straight



U-shaped curve




O-shaped curve




New Delac (for hospital ward applications)



Allowable load:
10 kg (22 lb)



Rail Cross Section



IV Roller Dimensions

Silver



White



Materials and Finishes

Parts		Material	Finish
Rail		Aluminum alloy extrusion material	Alumite
IV Roller	Wheel	Acetal resin	—
	Hook	SUS 304 Ø5	


New Delac Rails

Size		Product Code	
		Silver	White
1.82 m (72")		00210120	00210346
2.00 m (79")		00210121	00210347
2.73 m (107")		00210122	00210348
3.00 m (118")		00210123	00210349
3.64 m (143")		00210124	00210350
4.00 m (157")		00210125	00210351
Curved Rail (180 mmR/ 7.1"R)	0.40 m x 0.40 m (16" x 16")	00210126	————
	1.00 m x 1.00 m (39" x 39")	00210035	————


Supertrac (for ICU, CCU and operating room applications)



Allowable load:
10 kg (22 lb)



Rail Cross Section



IV Roller Dimensions

Silver



White



Materials and Finishes

Parts		Material	Finish
Rail		Aluminum alloy extrusion material	Alumite
IV Roller	Wheel	Special resin	—
	Hook	SUS 304 Ø6	

Supertrac Rails

Size	Product Code	
	Silver	White
3.00 m (118")	00240023	00240087
4.00 m (157")	00240026	00240088
Curved Rail (500 mmR/20"R) 1.00 m x 1.00 m (39" x 39") (Ordered separately) *1	00240058	—

*1 Curved 1.00 m x 1.00 m (39" x 39") rails (ordered separately) are 500 mmR (20"R).
Note: Possible radius sizes..... Silver: 450 mmR (18"R), 800 mmR (31") or more

Common Parts



1-hook

3-hook

5-hook

IV Bottles Hooks

1-hook, 3-hook and 5-hook hangers are available, each in two lengths, for a total of six types. The hanger length of the 5-hook type can be adjusted. And the hooks on the 3- and 5-hook types are foldable for convenience when carrying and storing.

Specifications

Products	Hooks	Extension Range	Length	Allowable Load	Materials and Finishes
B1000-P5	5-hook	638 mm (25") ⇔ 1000 mm (39")	1000 mm (39")	Lower hook: 5 kg (11 lb) Intermediate hooks: 1 kg (2.2 lb)	Aluminum, Acetal, Zinc die casting
B1200-P5		738 mm (29") ⇔ 1200 mm (47")	1200 mm (47")		
A600-P3	3-hook	_____	600 mm (24")	Lower hook: 5 kg (11 lb) Intermediate hooks: 1 kg (2.2 lb)	SUS 304 Ø6
A800-P3		_____	800 mm (31")		
A600-P1	1-hook	_____	600 mm (24")	Lower hook: 5 kg (11 lb)	
A800-P1		_____	800 mm (31")		


IV Wall Hooks

Slow Return function
slowly retracts the hook.

For easier removal of intravenous bottles or bags, the hook retracts slowly so that it does not impede the hand.



Allowable load:
10 kg (22 lb)



Precautions when mounting IV Hooks


*Securely attach each hook with two of the supplied 3.5 mm (.14") x 25 mm (.98") pan-head screws.

*To assure hooks remain firmly attached, mount on plywood at least 12 mm (.47") thick or on another substrate of the same thickness.


Precautions Concerning IV Hooks

*Securely attach each hook with three of the supplied 4.0 mm (.16") x 40 mm (1.6") pan-head screws.

The weight of an IV bottle causes the runner to lock, but it unlocks if the IV hanger is gently lifted, allowing the runner to move smoothly. Special plastic used for the runner wheels assures the runners are extremely quiet.




Unlocked



Locked

IV Hook Dimensions

<Fixed type> <30GN fixed type>





Allowable load:
10 kg (22 lb)

30GN fixed type features


*As a safety feature, the hook comes apart for when loads of 30 kg (66 lb) or more are applied.

*Be aware that even with loads lighter than 30 kg (66 lb), dynamic load may cause a hook to become detached.

New Delac Parts for IV

Product Name		Product Code
New Delac IV Roller		00210052
Allowable load: 10 kg (22 lb)		
New Delac End Stop B		Silver 00210135
		White 00210332
New Delac Splice (for Aluminum Rail)		00210128

Supertrac Parts for IV

Product Name		Product Code	Product Name		Product Code
Supertrac IV Roller		00240001	Supertrac End Stop		Silver 00240020
For a curve rail, use it together with a rail of 300 mmR (12"R) or longer.					
Supertrac End Cap		Silver 00240019	Supertrac Splice (for Aluminum rail)		00240004
		White 00240073			

IV Hooks

Product Name		Product Code	Product Name		Product Code
IV Bottles Hook		01080010	IV Bottles Hook	A600-P1	00450005
				A800-P1	00450004
Allowable load: 10 kg (22 lb)					
IV Bottles Hook 30GN		01080012	IV Bottles Hook	A600-P3	00450013
				A800-P3	00450015
Allowable load: 30 kg (66 lb)					
IV Wall Hook		01080013	IV Bottles Hook	B1000-P5	00450019
				B1200-P5	00450020
Allowable load: 10 kg (22 lb)					